

SL T2™ FACE SHIELD



H2MAX



DROPLET AND
SPLASH TEST

ENGINEERED PROTECTION THAT SURROUNDS

Elevate safety with the SL T2 Face Shield. Designed specifically for the SL T2 Safety Helmet, this clear face shield offers a wide field of view, providing clarity and precision in work environments. Effortlessly attaches to the SL T2 Safety Helmet for added convenience and protection.



FEATURES

Wide Field of View: Offers protection from potential hazards without compromising field of view, enhancing safety and productivity

Enhanced Safety: Constructed from robust materials, the shield frame and adapter protect and support face shield

User-Friendly Design: Ratchet clips make visor adjustments intuitive and efficient

Effortless Attachment: Attach and detach the face shield with ease, thanks to its quick-release/connect clip design that ensures a snug and secure fit every time

Maximum Anti-Fog Clarity: Treated with H2MAX to provide maximum clarity in extreme conditions while adding abrasion and chemical resistance, ensuring durable, waterproof vision even after repeated cleaning

Splash Safe: Passes D3: Droplet and Splash test

Engineered Toughness: Meets ANSI/ISEA Z87.1-2020 + high impact standard

i HPT2FV10 sold separately from the SL T2 Safety Helmet. Face Shield offers secondary protection and should be worn with safety eyewear or goggles.



TOOLS AT YOUR FINGERTIPS

Learn more about the SL T2 Helmet and Accessories

SL T2™ FACE SHIELD



H2MAX



DROPLET AND SPLASH TEST

ENGINEERED PROTECTION THAT SURROUNDS

Elevate safety with the SL T2 Face Shield. Designed specifically for the SL T2 Safety Helmet, this clear face shield offers a wide field of view, providing clarity and precision in work environments. Effortlessly attaches to the SL T2 Safety Helmet for added convenience and protection.

VARIATION

● HPT2FV10 Clear H2MAX AF



MATERIALS

Lens: PC (Polycarbonate)

Frame: ABS (Acrylonitrile Butadiene Styrene) Plastic

⚠ WARNING: Cancer and Reproductive Harm –P65Warnings.ca.gov

GENERAL SPECIFICATIONS

Weight: 145.5g

Overall Length: 227mm

Overall Width: 133mm

Lens Thickness: 1mm

Lens Base: 8.48mm

Vertical Lens Measurement: 177.5mm

MARKINGS

Standard: ANSI/ISEA Z87.1-2020 +

Part No.	Lens Marking	Lens Marking Symbols
HPT2FV10	KJ Z87+ U4 X D3	KJ: Manufacturer's Mark Z87: ANSI/ISEA Standard for Eye and Face Protection Devices +: High Impact U4: .04% Max Effective Far UV • .5% Max Near UV D3: Tested Droplet and Splash Test X: Tested Anti-Fog

Product markings may vary // Updated as of 06.24

INSTRUCTIONS

To Attach Clips to Helmet

1. Check for L and R indicators on the backside of each clip.
2. Place the left and right clips in the corresponding front accessory slots of the helmet.

To Attach Face Shield to Clips

1. Position the face shield over the holes on the clips.
2. Press in to ensure a secure fit.

To Remove Face Shield from Clips

1. Press the button labeled "PUSH" at the top of the clip.
2. Pull the shield out of the clip.

To Remove Clips from Helmet

1. Simply pull up on the clips to detach them from accessory slots.

To Remove Face Shield from Adapter

1. Locate the sliders on each side holding the shield to the adapter.
2. Push each slider back to unlock the shield.
3. Turn the face shield over to view the inside and unlock shield from the middle hook.

To Attach Face Shield to Adapter

1. To replace the shield, first attach the middle hook to back of adapter.
2. Align slots on the far edges, and slide sliders back into place.